

Desk Frame 5 (DF5)

Data Sheet





The Desk Frame 5 (DF5) offers a sturdy and robust solution for mounting DESKLIFT™ motor-housing systems, including EXPERIENCE™ systems, to your tabletop. Designed in a T-desk style, the DF5 is ideal for constructing both 2-legged frame solutions and bench setups.

The wide range of motor-housing columns allows desk manufacturers to design diverse desks based on the same top frame. The adjustable DF5 accommodates tabletops ranging from 1200 mm to 1800 mm, making it versatile for various office environments.

Assembly is straightforward, requiring only a few screws. Premounted rubber dampers help isolate vibrations between the tabletop and frame. Easily integrate columns, feet, power supplies, and controls to create a complete desk with our simple Plug & Play™ system.

Features/Accessories/Compatibility/Usage

Features

- Length: adjustable from 1154 mm to 1784 mm (fits tabletops from 1200 to 1800 mm)
- Oval holes, for optional use, ensure more flexibility when pre-drilling holes in tabletop
- Hole sizes facilitating the optional use of M6 machine screws for mounting the frame on the tabletop
- Mounting kit including screws for mounting the frame on the tabletop and cable holders for cable management
- Pre-mounted rubber dampers for isolation of vibrations between the tabletop and frame
- Cantilever length: 500 mm
- Max. total load (including the tabletop): 1600 N equally loaded, i.e. 800 N on each column
- Weight (approximate): 5.0 kg
- Colour: Available in black (RAL 9005), grey (RAL 9006), or white (RAL 9016)
- Available as set-packed delivery

Accessories

(for bench systems with DL5, DL6, DL18, DL19, DL20, or DL21 with bracket type H and V)

- Cross member set (including cross members for connecting the desks, all screws, and feet for bench solutions)
- Cable tray for cable management in bench systems
- Bridge for connecting of multiple bench systems

Compatibility

- All DESKLINE® motor-housing columns

Usage

- For indoor use in dry locations

Parameter	Operation	Storage and transportation
Temperature	10 to 40 °C	-10 to +50 °C
Relative humidity	20% to 80% - non-condensing	20% to 80% - non-condensing
Atmospheric pressure	800 to 1060 hPa	700 to 1060 hPa
Altitude	Max. 2000 m	N/A

- Can be used for T-desk (central placement of legs)
- Complies with EN527 for tabletops from 1200 mm to 1800 mm
- Complies with ANSI BIFMA X5.5 for tabletops from 1200 to 1800 mm length (if mounted using the BIFMA-compatible mounting kit)
- If a complete desk frame is required, use the DF5 together with DESKLIFT™ Feet (DLF) and a DL SetPack (DLS) solution

For system compliance, please refer to the Declaration of Conformity in the [User Manual](#) and the Data Sheets for [CBD6S](#), [SMPS001/SMPS002](#), [SMPS006](#), or [SMPS007](#).

Ordering

	DF5	
OPTION	0	0 = Standard
OPTION	0	0 = Standard
CANTILEVER	0	0 = T-desk
OPTION	0	0 = Standard
MOUNTING KIT	01	01 = Standard kit 02 = BIFMA-compatible kit
COLOUR	B	A = Grey (RAL 9006) B = Black (RAL 9005) D = White (RAL 9016)
FULLY RETRACTED LENGTH	1154	1154 = 1154 mm
FULLY EXTENDED LENGTH	1784	1784 = 1784 mm
DF5000001B11541784		

60 sets fit on a standard pallet.

Minimum order quantity is 60 sets.



To fulfil BIFMA compliance, please select Mounting kit option 02.

For further information on ordering DESKLIFT™ columns, please refer to our [website](#).

Mounting kits

Content	Standard kit (option 01) Item no. 1097W8002	BIFMA-compatible kit (option 02) Item no. 1097W8001
Panhead chipboard screws (Drive PZ2)	18 (4.5 x 16 mm)	22 (5 x 20 mm)
Bolt (M6 x 12 mm)	8	8
Cable relief	2	2
Cable holder	2	2
Rubber dampers for additional screws	0	4

Item numbers for standard products

Item number	Variant	Mounting kit	Colour
DF500001	Standard	01	Black (RAL 9005)
DF500002	Standard	01	White (RAL 9016)
DF500003	Standard	01	Grey (RAL 9006)
DF500004	BIFMA compatible	02	Black (RAL 9005)
DF500005	BIFMA compatible	02	White (RAL 9016)
DF500006	BIFMA compatible	02	Grey (RAL 9006)

Accessories



A cross-member set comprises all parts for joining together two desks into a bench system: 2 cross members, 4 threaded pins (M8 x 40 mm), 4 hex flange nuts, 4 bench feet, 8 mounting screws, and 4 adjustment screws.



Always select columns with bracket options H and V for the LINAK bench solution.

Cross members (set-packed)

Item number	Colour	Length (mm)
CM06A6201100	Grey (RAL 9006)	620
CM06B6201100	Black (RAL 9005)	620
CM06D6201100	White (RAL 9016)	620
CM06A8201100	Grey (RAL 9006)	820
CM06B8201100	Black (RAL 9005)	820
CM06D8201100	White (RAL 9016)	820

Pallet information:

Cross member length	620 mm	820 mm
Number of cross member packs	30	30
Weight (per set-pack)	5.2 kg	6.6 kg
Pallet weight (including pallet)	176 kg	218 kg
Dimensions (L x W x H)	1200 mm x 800 mm x 602 mm	1200 mm x 800 mm x 602 mm

Cable tray

Item number	Colour
SA0DF2T-00-120-870	Grey (RAL 9006)
SA0DF2T-00-001-870	Black (RAL 9005)
SA0DF2T-00-022-870	White (RAL 9016)

The cable tray is available as single-pack.

Pallet information:

Number of cable tray packs	30
Weight (per pack)	6.3 kg
Total weight (including pallet)	269 kg
Dimensions (L x W x H)	1200 mm x 800 mm x 1046 mm

Bridge for connection of two bench systems

Item number	Colour
SA1066W3012-120	Grey (RAL 9006)
SA1066W3012-001	Black (RAL 9005)
SA1066W3012-022	White (RAL 9016)

The bridge is available as single-pack.


Pallet information:

Number of bridge packs	70
Weight (per pack)	1.2 kg
Total weight (including pallet)	104 kg
Dimensions (L x W x H)	1200 mm x 800 mm x 981 mm

Dimension drawings



All dimensions are in mm.



Drawing no. 1097W4001

Figure 1 DF5 top frame (with cantilevers mounted)





Figure 2 DF5 cantilever

Drawing no. 1097W4002


Cross member



Drawing no. 1066W4030

Figure 3 Cross member


Bench foot



Drawing no. 1066W4033

Figure 4 Bench foot


Adjustment screw for bench foot



Drawing no. 1066W4034

Figure 5 Adjustment screw for bench foot


Cable tray



Drawing no. 1066W4060

Figure 6 Bench cable tray

Bridge



Drawing no. 1066W4041

Figure 7 Bench bridge

Contacts

FACTORIES

Denmark - Headquarters
LINAK A/S
Phone: +45 73 15 15 15
Fax: +45 74 45 80 48
Fax (Sales): +45 73 15 16 13
Web: www.linak.com

China
LINAK (Shenzhen) Actuator Systems, Ltd.
Phone: +86 755 8610 6656
Phone: +86 755 8610 6990
Web: www.linak.cn

Slovakia
LINAK Slovakia s.r.o.
Phone: +421 51 7563 444
Web: www.linak.sk

Thailand
LINAK APAC Ltd.
Phone: +66 33 265 400
Web: www.linak.com

USA
LINAK U.S. Inc.
Americas Headquarters
Phone: +1 502 253 5595
Fax: +1 502 253 5596
Web: www.linak-us.com
www.linak-latinamerica.com

SUBSIDIARIES

Australia
LINAK Australia Pty. Ltd
Phone: +61 3 8796 9777
Fax: +61 3 8796 9778
E-mail: sales@linak.com.au
Web: www.linak.com.au

Austria
LINAK Zweigniederlassung - Österreich (Wien)
Phone: +43 (1) 890 7446
Fax: +43 (1) 890 744615
E-mail: info@linak.de
Web: www.linak.at - www.linak.hu

Belgium
LINAK Actuator-Systems NV/SA
(Belgium & Luxembourg)
Phone: +32 (0)9 230 01 09
E-mail: beinfo@linak.be
Web: www.linak.be - www.fr.linak.be

Brazil
LINAK Do Brasil Comércio De Atuadores Ltda.
Phone: +55 (11) 2832 7070
Fax: +55 (11) 2832 7060
E-mail: info@linak.com.br
Web: www.linak.com.br

Canada
LINAK Canada Inc.
Phone: +1 502 253 5595
Fax: +1 416 255 7720
E-mail: info@linak.ca
Web: www.linak-us.com

Czech Republic
LINAK C&S s.r.o.
Phone: +42 058 174 1814
Fax: +42 058 170 2452
E-mail: info@linak.cz
Web: www.linak.cz - www.linak.sk

Denmark - International
LINAK International
Phone: +45 73 15 15 15
E-mail: info@linak.com
Web: www.linak.com

Denmark - Sales
LINAK Danmark A/S
Phone: +45 86 80 36 11
Fax: +45 86 82 90 51
E-mail: linak@linak-silkeborg.dk
Web: www.linak.dk

Finland
LINAK OY
Phone: +358 10 841 8700
E-mail: linak@linak.fi
Web: www.linak.fi

France
LINAK France E.U.R.L
Phone: +33 (0) 2 41 36 34 34
Fax: +33 (0) 2 41 36 35 00
E-mail: linak@linak.fr
Web: www.linak.fr

Germany
LINAK GmbH
Phone: +49 6043 9655 0
Fax: +49 6043 9655 60
E-mail: info@linak.de
Web: www.linak.de

India
LINAK A/S India Liaison Office
Phone: +91 120 4531797
Fax: +91 120 4786428
E-mail: info@linak.in
Web: www.linak.in

Italy
LINAK ITALIA S.r.l.
Phone: +39 02 48 46 33 66
Fax: +39 02 48 46 82 52
E-mail: info@linak.it
Web: www.linak.it

Japan
LINAK K.K.
Phone: 81-45-533-0802
Fax: 81-45-533-0803
E-mail: linak@linak.jp
Web: www.linak.jp

Malaysia
LINAK Actuators Sdn. Bhd.
Phone: +60 4 210 6500
Fax: +60 4 226 8901
E-mail: info@linak-asia.com
Web: www.linak.my

Netherlands
LINAK Actuator-Systems B.V.
Phone: +31 76 5 42 44 40 /
+31 76 200 11 10
E-mail: info@linak.nl
Web: www.linak.nl

New Zealand
LINAK New Zealand Ltd
Phone: +64 9580 2071
Fax: +64 9580 2072
E-mail: nzsales@linak.com.au
Web: www.linak.com.au

Norway
LINAK Norge AS
Phone: +47 32 82 90 90
E-mail: info@linak.no
Web: www.linak.no

Poland
LINAK Polska
LINAK Danmark A/S (Spółka Akcyjna)
Phone: +48 22 295 09 70 /
+48 22 295 09 71
E-mail: info@linak.pl
Web: www.linak.pl

Republic of Korea
LINAK Korea Ltd.
Phone: +82 2 6231 1515
Fax: +82 2 6231 1516
E-mail: info@linak.kr
Web: www.linak.kr

Slovakia
LINAK Slovakia S.R.O.
Phone: +421 51 7563 444
Web: www.linak.sk

Spain
LINAK Actuadores, S.L.U
Phone: +34 93 588 27 77
Fax: +34 93 588 27 85
E-mail: esma@linak.es
Web: www.linak.es

Sweden
LINAK Scandinavia AB
Phone: +46 8 732 20 00
Fax: +46 8 732 20 50
E-mail: info@linak.se
Web: www.linak.se

Switzerland
LINAK AG
Phone: +41 43 388 31 88
Fax: +41 43 388 31 87
E-mail: info@linak.ch
Web: www.linak.ch - www.fr.linak.ch
www.it.linak.ch

Taiwan
LINAK (Shenzhen) Actuator systems Ltd.
Taiwan Representative office
Phone: +886 2 272 90068
Fax: +886 2 272 90096
E-mail: sales@linak.com.tw
Web: www.linak.com.tw

Turkey
LINAK İth. İhr. San. ve Tic. A.Ş.
Phone: +90 312 4726338
Fax: +90 312 4726635
E-mail: info@linak.com.tr
Web: www.linak.com.tr

United Kingdom & Ireland
LINAK UK Limited
Phone: +44 (0)121 544 2211
Fax: +44 (0)121 544 2552
E-mail: sales@linak.co.uk
Web: www.linak.co.uk

DISTRIBUTORS

Argentina
Novotec Argentina SRL
Phone: 011-4303-8989 / 8900
Fax: 011-4032-0184
E-mail: info@novotecargentina.com
Web: www.novotecargentina.com

Colombia
MEM Ltda
Phone: +[57] (1) 334-7666
Fax: +[57] (1) 282-1684
E-mail: servicioalcliente@memltda.com.co
Web: www.mem.net.co

India
Mechatronics Control Equipments India Pvt Ltd
Phone: +91-44-28558484, 85
E-mail: bala@mechatronicscontrol.com
Web: www.mechatronicscontrol.com

Indonesia
PT. Himalaya Everest Jaya
Phone: +6 221 544 8956 /+6 221 544 8965
Fax: +6 221 619 1925
Fax (Sales): +6 221 619 4658
E-mail: hejplastic-div@centrin.net.id
Web: www.hej.co.id

Israel
NetivTech LTD
Phone: +972 55-2266-535
Fax: +972 2-9900-560
Email: info@NetivTech.com
Web: www.netivtech.com

Singapore
Servo Dynamics Pte Ltd
Phone: +65 6844 0288
Fax: +65 6844 0070
E-mail: servodynamics@servo.com.sg

South Africa
Industrial Specialised Applications CC
Phone: +27 011 466 0346
E-mail: gartht@isagroup.co.za
Web: www.isaza.co.za

United Arab Emirates
Mechatronics
Phone: +971 4 267 4311
Fax: +971 4 267 4312
E-mail: mechtron@emirates.net.ae

Terms of use

LINAK® takes great care in providing accurate and up-to-date information on its products. However, the user is responsible for determining the suitability of LINAK products for a specific application. Due to continual development, LINAK products are subject to frequent modifications and changes. LINAK reserves the rights to conduct modifications, updates, and changes without any prior notice. For the same reason, LINAK cannot guarantee the correctness and actual status of imprinted information on its products.

LINAK uses its best efforts to fulfil orders. However, for the reasons mentioned above, LINAK cannot guarantee availability of any particular product at any given time. LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or in other written material created and produced by LINAK, LINAK subsidiaries, or LINAK affiliates. All sales are subject to the 'Standard Terms of Sale and Delivery for LINAK A/S' available on LINAK websites. LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.