

OneConnect™ for Microsoft Windows **Installation Guide**



OneConnect™

Installation

1. Download OneConnect for Microsoft Windows from this link: <https://www.linak.com/pages/tools>
2. Click on the OneConnect for Microsoft Windows file and start installation
3. Follow instructions on screen
4. When installation is finished, you may be asked to restart your computer
5. For communication type 'extended OpenBus', you will need an IB30 Box: IB300001-01, 0964198-C cable (is included in the IB30 sales article) and a USB A-B cable.




Information

For communication type 'LCi cable', you will need an LCI2USB00 cable.


Overview



In the first menu, you can choose view to the connected type of control box.



For accessories and legacy control boxes, you need to import the views in the configuration menu.



Under the tab communication, you can choose communication type, if you connect with extended OpenBus (the IB30 Box) or the LCI cable (the LC12USB00 cable).

Under authorisation type, you have cloud authorisation for use with your OneConnect account.

Local authorisation is for use with offline keys.

Besides access to data read out, it gives access to system control.



Copyright© LINAK • 2025-09 • UT-61-02-062