

Foot Switch FS3

Data Sheet



Contents

Introduction..... 3

Features and options 4

Usage 4

Dimensions drawings 5

Ordering example 8

Contacts 9

Introduction



The LINAK® Foot Switch FS3 is an elegant control unit, allowing healthcare professionals across the sector to have both hands free when attending to patients, thus also helping to improve ergonomics. It is designed to be used in modular adjustment systems consisting of LINAK control boxes and electric LINAK IC actuators.

Developed in cooperation with end users, the FS3 is specifically designed to improve and ease control of applications, such as hospital beds, treatment couches/tables and various treatment chairs. The result is a particularly user-friendly and easy-to-clean unit with an elegant and aesthetic design.

However, the FS3 is also a very robust and durable foot control available in both a single and a double version. The latter allows you to add and control more movement options, often used in more advanced applications.

The FS3 is available in an analogue version as well as a digital OpenBus™ version, and for applications where trip hazards are an issue or design freedom is prioritised, the unit comes in a wireless edition too (Bluetooth® Low Energy).

The FS3 is likewise offered in a 3-stage variant that features an extra stop functionality. This FS3 version can be used in situations where an additional deactivation switch is preferable or required.

Description of the different activation levels on the 3-stage foot switch:

1. No activation - no pressure on the foot switch
2. Activation - normal pressure on the foot switch for application movement
3. Stop activation - increased pressure on the foot switch will stop the application movement



Features and options

Pedals colour:	Dark grey RAL7016
Bottom housing colour:	Light grey RAL 7035
Protection class:	IPX6 (or IPX6 Washable DURA™ for beds model only)
Number of functions:	1 or 2 functions
Cable:	Straight 1000 mm and 2000 mm, coiled 600 mm
Button type:	Easy touch tactile switches
Design:	Ergonomic design in the butterfly shape
Mounting:	Floor model or mounted on the side of the bed frame
Wireless:	Wireless operation together with CA/CO with BLE - floor model only
FS3, 3-stage switch:	Additional deactivation functionality - compatible with analogue LINAK control boxes

Usage

Usage temperature:	+ 5° C to + 40° C
Storage temperature:	-10° C to + 50° C
Relative humidity:	20% to 80% - non-condensing
Atmospheric pressure:	700 to 1060 hPa
Height above sea level:	Max. 3000 meters
Compatibility:	Compatible with LINAK analogue and OpenBus™ control boxes. Please contact LINAK.

Approvals:

Safety

- IEC60601-1
- ANSI/AAMI ES60601-1
- CAN/CSA-22.2 No. 60601-1



Radio

- RED
- FCC (US)
- IC (Canada)
- Telec (Japan)






Dimensions drawings


Dimensions for 1 channel floor model




Dimensions for 1 channel bed model




Dimensions for 2 channel floor model



Dimensions for 2 channel bed model with cable (analogue and OpenBus versions)




Dimensions for single FS3 wireless version



Drawing no.: 05801w4001

Dimensions for double FS3 wireless version



Drawing no.: 05801w4002

Ordering example

F S 3 2 0 1 2 0 0 0 0 0 6 - G 0 0 0 0 0 0 0 D 0 1 0 0 0		
	Not used	0 = None
	FS3 cable length:	0 = No cable (only wireless version) 1 = Straight 2000 mm 2 = Straight 1000 mm 3 = Coil 600 mm (only for OB variants) X = Special
	FS3 cable material	0 = No cable (only wireless version) 1 = PU 2 = TPE (only for FS3 3-stage version)
	FS3 cable plug type	D = DIN M = Modular N = No plug, wireless
	FS3 cable colour	0 = Grey RAL7035 1 = No cable (only wireless version)
	Not used	0 = None
	Interconnection cable	0 = None 1 = 1400 mm (only for bed adapter) 2 = 300 mm (only for bed adapter)
	Not used	0 = None
	Foot pedal handle colour	0 = Dark grey RAL7016 S = Special
	Mounting	0 = No screw (floor adapter single and double) 1 = Screw mounting (bed adapter single and double) 2 = No screw (wireless floor adapter single and double)
	Box colour	G = Grey RAL7035 B = Black RAL 9005 (only wireless version) W = White RAL 9016 (only wireless version) - = None
	IP-degree:	6 = IPX6 (floor version and wireless floor version) W = IPX6 Washable DURA™ (only bed version)
	Not used	0 = None
	Bluetooth generation	0 = LINAK GEN1 (no longer available for ordering) 4 = LINAK GEN2
	Not used	0 = None
	Functionality right pedal (right/double pedal)	0 = Only for OpenBus™ See functionality overview 1 = See functionality overview 2 = See functionality overview 3 = Not for OpenBus™ See functionality overview 4 = Not for OpenBus™ See functionality overview 5 = See functionality overview wireless X = Special
	Functionality left pedal (left/single pedal)	S = Single pedal 0 = Only for OpenBus™ See functionality overview 1 = See functionality overview 2 = See functionality overview 3 = Not for OpenBus™ See functionality overview 4 = Not for OpenBus™ See functionality overview 5 = See functionality overview wireless X = Special
	Functionality type	0 = Analogue (CB6 like control box, common positive) H = Analogue (Common Ground, CB9 like control box must choose this bit) V = OpenBus™ A = Wireless SW1 B = Wireless SW2 C = Wireless SW3 E = FS3 3-stage, CA analogue X = Special SW
	FS3 Type	0 = Bed adapter (single) 1 = Floor adapter (single) 2 = Floor adapter (double) 3 = Bed adapter (double) 4 = Floor wireless (single) 5 = Floor wireless (double)
	Controls Type	S3 = FS3
	Controls	F = Foot switch

FS3 3-stage is only available as single version foot switch.



Contacts

FACTORIES

Denmark - Headquarters

LINAK A/S

Phone: +45 73 15 15 15

Fax: +45 74 45 80 48

Fax (Sales): +45 73 15 16 13

Web: www.linak.com

China

LINAK (Shenzhen) Actuator Systems, Ltd.

Phone: +86 755 8610 6656

Phone: +86 755 8610 6990

Web: www.linak.cn

Slovakia

LINAK Slovakia s.r.o.

Phone: +421 51 7563 444

Web: www.linak.sk

Thailand

LINAK APAC Ltd.

Phone: +66 33 265 400

Web: www.linak.com

USA

LINAK U.S. Inc.

Americas Headquarters

Phone: +1 502 253 5595

Fax: +1 502 253 5596

Web: www.linak-us.com
www.linak-latinamerica.com

SUBSIDIARIES

Australia

LINAK Australia Pty. Ltd

Phone: +61 3 8796 9777

Fax: +61 3 8796 9778

E-mail: sales@linak.com.au

Web: www.linak.com.au

Austria

LINAK Zweigniederlassung - Österreich (Wien)

Phone: +43 (1) 890 7446

Fax: +43 (1) 890 744615

E-mail: info@linak.de

Web: www.linak.at - www.linak.hu

Belgium

LINAK Actuator-Systems NV/SA

(Belgium & Luxembourg)

Phone: +32 (0)9 230 01 09

E-mail: beinfo@linak.be

Web: www.linak.be - www.fr.linak.be

Brazil

LINAK Do Brasil Comércio De Atuadores Ltda.

Phone: +55 (11) 2832 7070

Fax: +55 (11) 2832 7060

E-mail: info@linak.com.br

Web: www.linak.com.br

Canada

LINAK Canada Inc.

Phone: +1 502 253 5595

Fax: +1 416 255 7720

E-mail: info@linak.ca

Web: www.linak-us.com

Czech Republic

LINAK C&S s.r.o.

Phone: +42 058 174 1814

Fax: +42 058 170 2452

E-mail: info@linak.cz

Web: www.linak.cz - www.linak.sk

Denmark - International

LINAK International

Phone: +45 73 15 15 15

E-mail: info@linak.com

Web: www.linak.com

Denmark - Sales

LINAK Danmark A/S

Phone: +45 86 80 36 11

Fax: +45 86 82 90 51

E-mail: linak@linak-silkeborg.dk

Web: www.linak.dk

Finland

LINAK OY

Phone: +358 10 841 8700

E-mail: linak@linak.fi

Web: www.linak.fi

France

LINAK France E.U.R.L

Phone: +33 (0) 2 41 36 34 34

Fax: +33 (0) 2 41 36 35 00

E-mail: linak@linak.fr

Web: www.linak.fr

Germany

LINAK GmbH

Phone: +49 6043 9655 0

Fax: +49 6043 9655 60

E-mail: info@linak.de

Web: www.linak.de

India

LINAK A/S India Liaison Office

Phone: +91 120 4531797

Fax: +91 120 4786428

E-mail: info@linak.in

Web: www.linak.in

Ireland

LINAK UK Limited (Ireland)

Phone: +44 (0)121 544 2211

Fax: +44 (0)121 544 2552

+44 (0)796 855 1606 (UK Mobile)

+35 387 634 6554 (Rep.of Ireland Mobile)

E-mail: sales@linak.co.uk

Web: www.linak.co.uk

Italy

LINAK ITALIA S.r.l.

Phone: +39 02 48 46 33 66

Fax: +39 02 48 46 82 52

E-mail: info@linak.it

Web: www.linak.it

Japan

LINAK K.K.

Phone: 81-45-533-0802

Fax: 81-45-533-0803

E-mail: linak@linak.jp

Web: www.linak.jp

Malaysia

LINAK Actuators Sdn. Bhd.

Phone: +60 4 210 6500

Fax: +60 4 226 8901

E-mail: info@linak-asia.com

Web: www.linak.my

Netherlands

LINAK Actuator-Systems B.V.

Phone: +31 76 5 42 44 40 /

+31 76 200 11 10

E-mail: info@linak.nl

Web: www.linak.nl

New Zealand

LINAK New Zealand Ltd

Phone: +64 9580 2071

Fax: +64 9580 2072

E-mail: nzsales@linak.com.au

Web: www.linak.com.au

Norway

LINAK Norge AS

Phone: +47 32 82 90 90

E-mail: info@linak.no

Web: www.linak.no

Poland

LINAK Polska

LINAK Danmark A/S (Spółka Akcyjna)

Phone: +48 22 295 09 70 /

+48 22 295 09 71

E-mail: info@linak.pl

Web: www.linak.pl

Republic of Korea

LINAK Korea Ltd.

Phone: +82 2 6231 1515

Fax: +82 2 6231 1516

E-mail: info@linak.kr

Web: www.linak.kr

Slovakia

LINAK Slovakia S.R.O.

Phone: +421 51 7563 444

Web: www.linak.sk

Spain

LINAK Actuadores, S.L.u

Phone: +34 93 588 27 77

Fax: +34 93 588 27 85

E-mail: esma@linak.es

Web: www.linak.es

Sweden

LINAK Scandinavia AB

Phone: +46 8 732 20 00

Fax: +46 8 732 20 50

E-mail: info@linak.se

Web: www.linak.se

Switzerland

LINAK AG

Phone: +41 43 388 31 88

Fax: +41 43 388 31 87

E-mail: info@linak.ch

Web: www.linak.ch - www.fr.linak.ch

www.it.linak.ch

Taiwan

LINAK (Shenzhen) Actuator systems Ltd.

Taiwan Representative office

Phone: +886 2 272 90068

Fax: +886 2 272 90096

E-mail: sales@linak.com.tw

Web: www.linak.com.tw

Turkey

LINAK İth. İhr. San. ve Tic. A.Ş.

Phone: +90 312 4726338

Fax: +90 312 4726635

E-mail: info@linak.com.tr

Web: www.linak.com.tr

United Kingdom

LINAK UK Limited

Phone: +44 (0)121 544 2211

Fax: +44 (0)121 544 2552

E-mail: sales@linak.co.uk

Web: www.linak.co.uk

DISTRIBUTORS

Argentina

Novotec Argentina SRL

Phone: 011-4303-8989 / 8900

Fax: 011-4032-0184

E-mail: info@novotecargentina.com

Web: www.novotecargentina.com

Colombia

MEM Ltda

Phone: +[57] (1) 334-7666

Fax: +[57] (1) 282-1684

E-mail: servicioalcliente@memltda.com.co

Web: www.mem.net.co

India

Mechatronics Control Equipments India Pvt Ltd

Phone: +91-44-28558484, 85

E-mail: bala@mechatronicscontrol.com

Web: www.mechatronicscontrol.com

Indonesia

PT. Himalaya Everest Jaya

Phone: +6 221 544 8956 /+6 221 544 8965

Fax: +6 221 619 1925

Fax (Sales): +6 221 619 4658

E-mail: hejplastic-div@centrin.net.id

Web: www.hej.co.id

Israel

NetivTech LTD

Phone: +972 55-2266-535

Fax: +972 2-9900-560

Email: info@NetivTech.com

Web: www.netivtech.com

Singapore

Servo Dynamics Pte Ltd

Phone: +65 6844 0288

Fax: +65 6844 0070

E-mail: servodynamics@servo.com.sg

South Africa

Industrial Specialised Applications CC

Phone: +27 011 466 0346

E-mail: gartht@isagroup.co.za

Web: www.isaza.co.za

United Arab Emirates

Mechatronics

Phone: +971 4 267 4311

Fax: +971 4 267 4312

E-mail: mechtron@emirates.net.ae

Terms of use

LINAK® takes great care in providing accurate and up-to-date information on its products. However, the user is responsible for determining the suitability of LINAK products for a specific application. Due to continual development, LINAK products are subject to frequent modifications and changes. LINAK reserves the rights to conduct modifications, updates, and changes without any prior notice. For the same reason, LINAK cannot guarantee the correctness and actual status of imprinted information on its products.

LINAK uses its best efforts to fulfil orders. However, for the reasons mentioned above, LINAK cannot guarantee availability of any particular product at any given time. LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or in other written material created and produced by LINAK, LINAK subsidiaries, or LINAK affiliates. All sales are subject to the 'Standard Terms of Sale and Delivery for LINAK A/S' available on LINAK websites. LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.