

DESKLIFT™ Feet (DLF)

Data Sheet





DESKLIFT™ Feet (DLF) are designed to offer reliable support for office desks. The feet are available in various types:

Desk design

- T-desk
- C-desk

Length

- 560 mm (22 inches)
- 710 mm (28 inches)

Standard colour

- Black
- Grey
- White

The feet are compatible with a wide range of LINAK® columns, offering flexibility in design and functionality. The DLF blend perfectly into various office desk designs thanks to the three different and discrete designs:

- On-top - the simplest way to mount foot and column
- Recessed - ensures the lowest built-in height
- Click-on - ideal for end-user assembly; no need for tools - just click foot on column

With the feet, the DL set-packed solution, and a Kick & Click™ top frame (Desk Frame 1) or a Desk Frame 2, you have a complete desk frame. The numerous combination possibilities meet any design requirement for modern height-adjustable office desks.

Features/Options/Compatibility/Usage

Features

Common

- Lengths:
 - 560 mm (22")
 - 710 mm (28")
- Colour: Available in black (RAL 9005), grey (RAL 9006) or white (RAL 9016)
- Compatible with T-desk and C-desk designs

On-top and recessed versions

- Two designs: for on-top or recessed mounting
- Several widths optimised for different column types
- Height: 43.6 mm
- Weight:
 - Approx. 1.4 to 2.9 kg (per foot)
 - Approx. 3.0 to 6.0 kg (set-pack)
- Delivery:
 - Set-packed delivery (including adjustment screws and mounting screws for the column)
 - Bulk delivery

Click-on version

- Simple click-on mounting (no tools needed for mounting)
- Width: 75 mm (fits various columns)
- Height: 21 mm (supports BIFMA compliance)
- Weight:
 - Approx. 2.2 to 2.8 kg (per foot)
 - Approx. 4.7 to 5.8 kg (set-pack)
- Delivery:
 - Set-packed delivery (including pre-mounted adjustment screws)

Bench feet

- Simple foot for bench systems

Options

- Customised colours

Compatibility

- Kick & Click™ (Desk Frame 1) - T-desk and C-desk designs
- Desk Frame 2

On-top and recessed versions

- Motor-housing columns DL5, DL6, DL10, DL11, DL18, and DL19 (standard and IC versions)
- Inline columns DL14 and DL17
- Desk Frame 2 columns DF2L06 and DF2L19

Click-on version

- Motor-housing PLUS™ columns DL6, DL19, and DL21 (standard and IC versions)
- Desk Frame 2 columns DF2L06 and DF2L19

Bench feet

- Motor-housing columns DL5, DL6, DL10, DL11, DL18, and DL19 (standard and IC versions)
- Inline columns DL14 and DL17
- Desk Frame 2 columns DF2L06 and DF2L19

Usage

On-top and recessed versions

- Tested in accordance with EN527-1, EN527-2 and ANSI BIFMA 5.5 in connection with a Kick & Click™ top frame

Click-on version

- Compliant with desk norms (EN 527-2 and ANSI BIFMA 5.5)

Ordering



Feet for DL10/DL11 also fit DL14, and feet for DL18/DL19 also fit DL17.
We do not have a top frame solution for these inline columns.

T-desk design

Set-packed deliveries

On-top and recessed versions available

Column	Article number	Combination code	Length (mm/inch)	Colour	Mounting On top (T) Recessed (R)
DL10, DL11, DL18, DL19, DF2L19	DLF00007	DLF19111A710000	710/28	Grey	T
	DLF00008	DLF19111B710000		Black	
	DLF00009	DLF19111D710000		White	
	DLF00010	DLF19111A560000	560/22	Grey	
	DLF00011	DLF19111B560000		Black	
	DLF00012	DLF19111D560000		White	
DL5, DL6, DF2L06	DLF00001	DLF06111A710000	710/28	Grey	
	DLF00002	DLF06111B710000		Black	
	DLF00003	DLF06111D710000		White	
	DLF00004	DLF06111A560000	560/22	Grey	
	DLF00005	DLF06111B560000		Black	
	DLF00006	DLF06111D560000		White	
DL18, DL19 DF2L19	DLF00025	DLF19211A710000	710/28	Grey	R
	DLF00026	DLF19211B710000		Black	
	DLF00027	DLF19211D710000		White	
	DLF00028	DLF19211A560000	560/22	Grey	
	DLF00029	DLF19211B560000		Black	
	DLF00030	DLF19211D560000		White	
DL10, DL11	DLF00019	DLF11211A710000	710/28	Grey	
	DLF00020	DLF11211B710000		Black	
	DLF00021	DLF11211D710000		White	
	DLF00022	DLF11211A560000	560/22	Grey	
	DLF00023	DLF11211B560000		Black	
	DLF00024	DLF11211D560000		White	
DL5, DL6, DF2L06	DLF00013	DLF06211A710000	710/28	Grey	
	DLF00014	DLF06211B710000		Black	
	DLF00015	DLF06211D710000		White	
	DLF00016	DLF06211A560000	560/22	Grey	
	DLF00017	DLF06211B560000		Black	
	DLF00018	DLF06211D560000		White	

Black: RAL 9005

Grey: RAL 9006

White: RAL 9016



60 sets fit on a standard pallet

Bulk deliveries**On-top and recessed versions available**

Column	Article number	Order quantity (per pallet)	Length (mm / inch)	Colour	Mounting On top (T) Recessed (R)
DL10, DL11, DL18, DL19, DF2L19	SA1037W9162-710-120	120	710 / 28	Grey	T
	SA1037W9162-710-001			Black	
	SA1037W9162-710-022			White	
	SA1037W9163-560-120	120	560 / 22	Grey	
	SA1037W9163-560-001			Black	
	SA1037W9163-560-022			White	
DL5, DL6, DF2LS06	sA1037W9166-710-120	120	710 / 28	Grey	
	SA1037W9166-710-001			Black	
	SA1037W9166-710-022			White	
	SA1037W9167-560-120	120	560 / 22	Grey	
	SA1037W9167-560-001			Black	
	SA1037W9167-560-022			White	
DL18, DL19, DF2L19	SA1037W9185-710-120	120	710 / 28	Grey	R
	SA1037W9185-710-001			Black	
	SA1037W9185-710-022			White	
	SA1037W9184-560-120	120	560 / 22	Grey	
	SA1037W9184-560-001			Black	
	SA1037W9184-560-022			White	
DL10, DL11	SA1037W9183-710-120	120	710 / 28	Grey	
	SA1037W9183-710-001			Black	
	SA1037W9183-710-022			White	
	SA1037W9182-560-120	120	560 / 22	Grey	
	SA1037W9182-560-001			Black	
	SA1037W9182-560-022			White	
DL5, DL6, DF2LS06	SA1037W9187-710-120	120	710 / 28	Grey	
	SA1037W9187-710-001			Black	
	SA1037W9187-710-022			White	
	SA1037W9186-560-120	120	560 / 22	Grey	
	SA1037W9186-560-001			Black	
	SA1037W9186-560-022			White	

Black: RAL 9005

Grey: RAL 9006

White: RAL 9016

Accessories for feet (bulk deliveries)

Screws for on-top and recessed feet (must be ordered separately).

Type of screw	Article number	Pieces needed
Adjustment screw ø40 mm (M8x18)	SA1037W9902	2
Mounting screw for the column (M6x16)	SA1037W9901	4

C-desk design

Set-packed deliveries

On-top and recessed versions available

Column	Combination code	Length (mm/inch)	Colour	Mounting On top (T) Recessed (R)
DL18, DL19, DF2L19	DLF19121A710000	710/28	Grey	T
	DLF19121B710000		Black	
	DLF19121D710000		White	
	DLF19121A560000	560/22	Grey	
	DLF19121B560000		Black	
	DLF19121D560000		White	
DL5, DL6, DF2L06	DLF06121A710000	710/28	Grey	
	DLF06121B710000		Black	
	DLF06121D710000		White	
	DLF06121A560000	560/22	Grey	
	DLF06121B560000		Black	
	DLF06121D560000		White	
DL5, DL6, DF2L06	DLF06221A710000	710/28	Grey	R
	DLF06221B710000		Black	
	DLF06221D710000		White	
	DLF06221A560000	560/22	Grey	
	DLF06221B560000		Black	
	DLF06221D560000		White	

Black: RAL 9005

Grey: RAL 9006

White: RAL 9016



60 sets fit on a standard pallet

Bulk deliveries**On-top and recessed versions available**

Column	Article number	Order quantity (per pallet)	Length (mm / inch)	Colour	Mounting On top (T) Recessed (R)
DL10, DL11, DL18, DL19, DF2L19	SA1037W9405-710-120	120	710 / 28	Grey	T
	SA1037W9405-710-001			Black	
	SA1037W9405-710-022			White	
	SA1037W9404-560-120	120	560 / 22	Grey	
	SA1037W9404-560-001			Black	
	SA1037W9404-560-022			White	
DL5, DL6, DF2LS06	SA1037W9403-710-120	120	710 / 28	Grey	
	SA1037W9403-710-001			Black	
	SA1037W9403-710-022			White	
	SA1037W9402-560-120	120	560 / 22	Grey	
	SA1037W9402-560-001			Black	
	SA1037W9402-560-022			White	
DL5, DL6, DF2LS06	SA1037W9411-710-120	120	710 / 28	Grey	R
	SA1037W9411-710-001			Black	
	SA1037W9411-710-022			White	
	SA1037W9410-560-120	120	560 / 22	Grey	
	SA1037W9410-560-001			Black	
	SA1037W9410-560-022			White	

Black: RAL 9005

Grey: RAL 9006

White: RAL 9016

Accessories for feet (bulk deliveries)

Screws for on-top and recessed feet (must be ordered separately).

Type of screw	Article number	Pieces needed
Adjustment screw ø40 mm (M8x18)	SA1037W9902	2
Mounting screw for the column (M6x16)	SA1037W9901	4

Click-on Feet



Click-on Feet are available for T-desk designs.



Click-on Feet are not available as bulk deliveries.
The adjustment screws are pre-mounted on the feet.

Set-packed deliveries

Column	Article number	Combination code	Length (mm / inch)	Colour
DL6, DF2L06, DL19, DF2L19, DL21	DLF00053	DLF00110A710000	710 / 28	Grey
	DLF00054	DLF00110B710000		Black
	DLF00055	DLF00110D710000		White
	DLF00056	DLF00110A560000	560 / 22	Grey
	DLF00057	DLF00110B560000		Black
	DLF00058	DLF00110D560000		White

Bench feet

The bench foot and related mounting and adjustments screws for the DESKLINE bench solution are part of the cross member set compatible with column bracket types H and V.

For other applications the bench-foot parts can be ordered as bulk delivery.

Bulk deliveries

Item	Bulk article numbers	Minimum order quantity
Bench foot	SA1066W3014-001	360
M8 x 14 mm mounting screws	SA0002747	500
M8 x 10 mm adjustment screws	SA1066W1024	1000



The bench foot is available in black.

Ordering and delivery information

Set-packed solutions for on-top and recessed versions consist of:

- 2 feet
- 4 x adjustment screws (ø40 mm)
- 8 x M6 mounting screws for the column

Set-packed solutions for the Click-on version consist of:

- 2 feet with pre-mounted adjustment screws

Technical data

Weight

Type of DESKLIFT™ Feet	Per foot (kg)	Per set-pack (kg)
DL5, DL6, DF2LS06 columns, on top mounted, short	1.4	3.0
DL5, DL6, DF2LS06 columns, on top mounted, long	1.8	3.8
DL5, DL6, DF2LS06 columns, recessed mounted, short	1.8	3.9
DL5, DL6, DF2LS06 columns, recessed mounted, long	2.3	4.9
DL10, DL11, DL14, DL17, DL18, DL19, on top mounted, short	1.7	3.6
DL10, DL11, DL14, DL17, DL18, DL19, on top mounted, long	2.1	4.4
DL10, DL11, DL14, recessed mounted, short	2.3	4.8
DL10, DL11, DL14, recessed mounted, long	2.9	6.0
DL17, DL18, DL19, recessed mounted, short	2.3	4.8
DL17, DL18, DL19, recessed mounted, long	2.9	6.0
Click-on, short	2.2	4.7
Click-on, long	2.8	5.8

Table 1 Approximate weight for feet (T-desk design)



A foot for C-desk design weighs approximately 0.3 kg more than the corresponding foot for T-desk design

Dimension drawings




All dimensions are in mm.

T-desk design

Mounted on top


Feet for DL5/DL6/DF2L06 columns



Assemble with colum
using 4 pcs. M6 screws.

Drawing no.1037W4022

Figure 2 Length: 560 mm




Assemble with colum
using 4 pcs. M6 screws

Drawing no.1037W4023

Figure 3 Length: 710 mm


Feet for DL10/DL11/DL14/DL17/DL18/DL19/DF2L19 columns



Assemble with colum
using 4 pcs. M6 screws

Drawing no.1037W4024

Figure 4 Length: 560 mm




Assemble with colum
using 4 pcs. M6 screws.

Drawing no.1037W4025

Figure 5 Length: 710 mm

Recessed mounted

Feet for DL5/DL6/DF2L06 columns




Assemble with column
using 4 pcs. M6 screws.



Figure 6 Length: 560 mm

Drawing no.1037W4030



Assemble with column
using 4 pcs. M6 screws.




Figure 7 Length: 710 mm

Drawing no.1037W4031

Feet for DL17/DL18/DL19/DF2L19 columns




Figure 10 Length: 560 mm

Drawing no.1037W4035




Figure 11 Length: 710 mm

Drawing no.1037W4036

Feet for DL10/DL11/DL14 columns




Figure 8 Length: 560 mm

Drawing no.1037W4033




Figure 9 Length: 710 mm

Drawing no.1037W4034

C-desk design

Mounted on top

Feet for DL5/DL6/DF2L06 columns




Figure 12 Length: 560 mm

Drawing no.1037W4026





Figure 13 Length: 710 mm


Drawing no.1037W4027

Feet for DL10/DL11/DL14/DL17/DL18/DL19/DF2L19 columns



Drawing no.1037W4028


Figure 14 Length: 560 mm



Drawing no.1037W4029


Figure 15 Length: 710 mm

Recessed mounted
Feet for DL5/DL6/DF2L06 columns



Drawing no.1037W4021


Figure 16 Length: 560 mm



Drawing no.1037W4020

Figure 17 Length: 710 mm

Adjustment screw for on-top and recessed foot



Drawing no.1037W4032

Figure 18 Adjustment screw for on-top and recessed foot

Click-on

Feet for DL6/DF2L06/DL19/DF2L19/DL21 columns




Figure 19 Length: 560 mm

Drawing no.1073W4002





Figure 20 Length: 710 mm

Drawing no.1073W4003


Bench foot



Drawing no. 1066W4033

Figure 21 Bench foot

Adjustment screw for bench foot



Drawing no. 1066W4034

Figure 22 Adjustment screw for bench foot

Contacts

FACTORIES

Denmark - Headquarters
LINAK A/S
Phone: +45 73 15 15 15
Fax: +45 74 45 80 48
Fax (Sales): +45 73 15 16 13
Web: www.linak.com

China
LINAK (Shenzhen) Actuator Systems, Ltd.
Phone: +86 755 8610 6656
Phone: +86 755 8610 6990
Web: www.linak.cn

Slovakia
LINAK Slovakia s.r.o.
Phone: +421 51 7563 444
Web: www.linak.sk

Thailand
LINAK APAC Ltd.
Phone: +66 33 265 400
Web: www.linak.com

USA
LINAK U.S. Inc.
Americas Headquarters
Phone: +1 502 253 5595
Fax: +1 502 253 5596
Web: www.linak-us.com
www.linak-latinamerica.com

SUBSIDIARIES

Australia
LINAK Australia Pty. Ltd
Phone: +61 3 8796 9777
Fax: +61 3 8796 9778
E-mail: sales@linak.com.au
Web: www.linak.com.au

Austria
LINAK Zweigniederlassung - Österreich (Wien)
Phone: +43 (1) 890 7446
Fax: +43 (1) 890 744615
E-mail: info@linak.de
Web: www.linak.at - www.linak.hu

Belgium
LINAK Actuator-Systems NV/SA
(Belgium & Luxembourg)
Phone: +32 (0)9 230 01 09
E-mail: beinfo@linak.be
Web: www.linak.be - www.fr.linak.be

Brazil
LINAK Do Brasil Comércio De Atuadores Ltda.
Phone: +55 (11) 2832 7070
Fax: +55 (11) 2832 7060
E-mail: info@linak.com.br
Web: www.linak.com.br

Canada
LINAK Canada Inc.
Phone: +1 502 253 5595
Fax: +1 416 255 7720
E-mail: info@linak.ca
Web: www.linak-us.com

Czech Republic
LINAK C&S s.r.o.
Phone: +42 058 174 1814
Fax: +42 058 170 2452
E-mail: info@linak.cz
Web: www.linak.cz - www.linak.sk

Denmark - International
LINAK International
Phone: +45 73 15 15 15
E-mail: info@linak.com
Web: www.linak.com

Denmark - Sales
LINAK Danmark A/S
Phone: +45 86 80 36 11
Fax: +45 86 82 90 51
E-mail: linak@linak-silkeborg.dk
Web: www.linak.dk

Finland
LINAK OY
Phone: +358 10 841 8700
E-mail: linak@linak.fi
Web: www.linak.fi

France
LINAK France E.U.R.L
Phone: +33 (0) 2 41 36 34 34
Fax: +33 (0) 2 41 36 35 00
E-mail: linak@linak.fr
Web: www.linak.fr

Germany
LINAK GmbH
Phone: +49 6043 9655 0
Fax: +49 6043 9655 60
E-mail: info@linak.de
Web: www.linak.de

India
LINAK A/S India Liaison Office
Phone: +91 120 4531797
Fax: +91 120 4786428
E-mail: info@linak.in
Web: www.linak.in

Italy
LINAK ITALIA S.r.l.
Phone: +39 02 48 46 33 66
Fax: +39 02 48 46 82 52
E-mail: info@linak.it
Web: www.linak.it

Japan
LINAK K.K.
Phone: 81-45-533-0802
Fax: 81-45-533-0803
E-mail: linak@linak.jp
Web: www.linak.jp

Malaysia
LINAK Actuators Sdn. Bhd.
Phone: +60 4 210 6500
Fax: +60 4 226 8901
E-mail: info@linak-asia.com
Web: www.linak.my

Netherlands
LINAK Actuator-Systems B.V.
Phone: +31 76 5 42 44 40 /
+31 76 200 11 10
E-mail: info@linak.nl
Web: www.linak.nl

New Zealand
LINAK New Zealand Ltd
Phone: +64 9580 2071
Fax: +64 9580 2072
E-mail: nzsales@linak.com.au
Web: www.linak.com.au

Norway
LINAK Norge AS
Phone: +47 32 82 90 90
E-mail: info@linak.no
Web: www.linak.no

Poland
LINAK Polska
LINAK Danmark A/S (Spółka Akcyjna)
Phone: +48 22 295 09 70 /
+48 22 295 09 71
E-mail: info@linak.pl
Web: www.linak.pl

Republic of Korea
LINAK Korea Ltd.
Phone: +82 2 6231 1515
Fax: +82 2 6231 1516
E-mail: info@linak.kr
Web: www.linak.kr

Slovakia
LINAK Slovakia S.R.O.
Phone: +421 51 7563 444
Web: www.linak.sk

Spain
LINAK Actuadores, S.L.u
Phone: +34 93 588 27 77
Fax: +34 93 588 27 85
E-mail: esma@linak.es
Web: www.linak.es

Sweden
LINAK Scandinavia AB
Phone: +46 8 732 20 00
Fax: +46 8 732 20 50
E-mail: info@linak.se
Web: www.linak.se

Switzerland
LINAK AG
Phone: +41 43 388 31 88
Fax: +41 43 388 31 87
E-mail: info@linak.ch
Web: www.linak.ch - www.fr.linak.ch
www.it.linak.ch

Taiwan
LINAK (Shenzhen) Actuator systems Ltd.
Taiwan Representative office
Phone: +886 2 272 90068
Fax: +886 2 272 90096
E-mail: sales@linak.com.tw
Web: www.linak.com.tw

Turkey
LINAK İth. İhr. San. ve Tic. A.Ş.
Phone: +90 312 4726338
Fax: +90 312 4726635
E-mail: info@linak.com.tr
Web: www.linak.com.tr

United Kingdom & Ireland
LINAK UK Limited
Phone: +44 (0)121 544 2211
Fax: +44 (0)121 544 2552
E-mail: sales@linak.co.uk
Web: www.linak.co.uk

DISTRIBUTORS

Argentina
Novotec Argentina SRL
Phone: 011-4303-8989 / 8900
Fax: 011-4032-0184
E-mail: info@novotecargentina.com
Web: www.novotecargentina.com

Colombia
MEM Ltda
Phone: +[57] (1) 334-7666
Fax: +[57] (1) 282-1684
E-mail: servicioalcliente@memltda.com.co
Web: www.mem.net.co

India
Mechatronics Control Equipments India Pvt Ltd
Phone: +91-44-28558484, 85
E-mail: bala@mechatronicscontrol.com
Web: www.mechatronicscontrol.com

Indonesia
PT. Himalaya Everest Jaya
Phone: +6 221 544 8956 /+6 221 544 8965
Fax: +6 221 619 1925
Fax (Sales): +6 221 619 4658
E-mail: hejplastic-div@centrin.net.id
Web: www.hej.co.id

Israel
NetivTech LTD
Phone: +972 55-2266-535
Fax: +972 2-9900-560
Email: info@NetivTech.com
Web: www.netivtech.com

Singapore
Servo Dynamics Pte Ltd
Phone: +65 6844 0288
Fax: +65 6844 0070
E-mail: servodynamics@servo.com.sg

South Africa
Industrial Specialised Applications CC
Phone: +27 011 466 0346
E-mail: gartht@isagroup.co.za
Web: www.isaza.co.za

United Arab Emirates
Mechatronics
Phone: +971 4 267 4311
Fax: +971 4 267 4312
E-mail: mechtron@emirates.net.ae

Terms of use

LINAK® takes great care in providing accurate and up-to-date information on its products. However, the user is responsible for determining the suitability of LINAK products for a specific application. Due to continual development, LINAK products are subject to frequent modifications and changes. LINAK reserves the rights to conduct modifications, updates, and changes without any prior notice. For the same reason, LINAK cannot guarantee the correctness and actual status of imprinted information on its products.

LINAK uses its best efforts to fulfil orders. However, for the reasons mentioned above, LINAK cannot guarantee availability of any particular product at any given time. LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or in other written material created and produced by LINAK, LINAK subsidiaries, or LINAK affiliates. All sales are subject to the 'Standard Terms of Sale and Delivery for LINAK A/S' available on LINAK websites. LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.