






B (Built-in length) [mm]	S (Stroke length) [mm]	O (Outer profile length) [mm]
445/450/455	300	420
495/500/505	350	470
645/650/655	500	620



Built-in length, stroke length, and outer profile length




Profile




Inner profile




3 mm bottom plate



3 mm top plate



8 mm bottom plate



8 mm top plate

All rights reserved

Date:

30 June 2026

Description:

DL2 Column

LINAK® 
WE IMPROVE YOUR LIFE