






Version	Combination code	B (Built-in length) [mm]	S (Stroke length) [mm]	O (Outer profile length) [mm]
EU	DL9xxxxxx650560	560	650	544
XL	DL9xxxxxx980730	730	980	709


Built-in length, stroke length, and outer profile length



Motor housing



Bottom plate



Profile dimensions (mm)

All rights reserved

Date:
02 September 2026

Description:

DL9

LINAK® 
WE IMPROVE YOUR LIFE