






B (Built-in length) [mm]	S (Stroke length) [mm]	O (Outer profile length) [mm]
645	500	590
445	300	390
345	200	290

Built-in length, stroke length, and outer profile length



Motor housing, bracket, and bottom plate



Profile

All rights reserved

Date:

17 August 2026

Description:

DL1A Column



WE IMPROVE YOUR LIFE