






Combination code	B (Built-in length) [mm]	S (Stroke length) [mm]	O (Outer profile length) [mm]
DL15xxxxxx500645	645	500	640


Built-in length, stroke length, and outer profile length



Motor housing



Bottom plate



Profile dimensions

All rights reserved

Date:
03 September 2026

Description:

DL15

LINAK®
WE IMPROVE YOUR LIFE