




Version	Combination code	B (Built-in length) [mm]	S (Stroke length) [mm]	O (Outer profile length) [mm]
EU	DL16xxxxxx650560	560	650	498
BIFMA	DL16xxxxxx665518	518	665	456
XL	DL16xxxxxx980730	730	980	709


Built-in length, stroke length, and outer profile length



Motor housing



Bottom plate



Profile dimensions

All rights reserved

Date:
03 September 2026

Description:

DL16

LINAK®
WE IMPROVE YOUR LIFE