

Safety Limit Switch SLS

Data Sheet



Contents

Introduction..... 3

Features and options 4

Usage 4

Ordering example 5

Dimensions 6

Cable lengths..... 7

Contacts 8

Introduction

There are 2 types of SLS switches, an analogue and an OpenBus™ type.

The analogue SLS can be used as safety feature to cut off the current to the actuator. The SLS is available with 1 or 2 switches (activated by the same button). It can be placed to prevent an unintentional positioning of the various frame segments in relation to each other or simply as an external limit switch to protect the frame against the full thrust of the actuator in end position. The actuator stops immediately when the button is pressed.

The OpenBus SLS is to be used together with the OpenBus control boxes.

It is available both as a passive and as an active type. It comes with 1 switch, Normally Open (NO). The standard OpenBus SLS is not to be used for safety (Signal Limit Switch).

Both types can be used as an external signal unit that gives a signal to the control box. This signal can limit or interrupt the functions on for instance a bed or can be used to start an OpenBus function.

Features and options

Compatibility:	Fully compatible with LINAK® systems
Housing:	Sturdy, grey plastic housing • To be mounted on the cable between the control box and the actuator LA28, LA28S, LA30, LA31 or LA34 (analogue SLS) • To be mounted directly on the OpenBus system (OpenBus SLS), on the control box or via an MJB
Mounting:	
Dimensions:	Small dimensions for easy installation
Voltage:	Rated at 5A / 24V DC (analogue)
Software:	Customised Software (OpenBus)
Protection class:	IPX6, IPX6 Washable
Colour:	Light grey (RAL 7035)

Usage

Usage temperature:	5 °C to 40 °C
Storage temperature	-10 °C to 50 °C
Atmospheric pressure:	700 to 1060 hPa
Height above sea level:	Max. 3000 meters
Approvals:	IEC60601-1 ANSI/AAMI ES60601-1 CAN/CSA-22.2 No 60601-1

Ordering example

SLS 0 0 0 + 0 100 0 100

CABLE LENGTH L2 (right)

Length in cm*	Jack	Din	No plug
000 = No cable (+ blind plug)			
100 = Straight, 1000mm	0015705	0015171-A	0015034 or
120 = Straight, 1200mm	0015705	0015171-A	0015036 for
150 = Straight, 1500mm	0015704	0015171-A	LA31
200 = Straight, 2000mm	0015704	0015171-A	
245 = Straight, 2450mm	0015704	0015171-A	
C20 = Coiled, 200mm	0015734	0015350	
C40 = Coiled, 400mm	0015736	(does not exist)	

PLUG TYPE for L2

- 0 = No plug
1 = Jack plug
2 = DIN plug (4P)
X = Other

CABLE LENGTH L1 (left)

Length in cm*	Jack	Din	MP(RJ50)	No plug
000 = No cable (+ blind plug)				
100 = Straight, 1000mm	0015705	0015171-A	0964050-A	0015034 or
120 = Straight, 1200mm	0015705	0015171-A	0964050-A	0015036 for
150 = Straight, 1500mm	0015704	0015171-A	0964050-A	LA31
200 = Straight, 2000mm	0015704	0015171-A	0964050-A	
245 = Straight, 2450mm	0015704	0015171-A		
C20 = Coiled, 200mm	0015734	0015350		
C40 = Coiled, 400mm	0015736	(does not exist)		

PLUG TYPE for L1

- 0 = No plug
1 = Jack plug
2 = DIN plug (4P)
3 = Modular Plug (RJ50 10 pins/5 wires, only for OpenBus function)
X = Other

COLOUR

- + = Grey
- = Black (does not exist yet)

ACTUATOR

- 0 = No actuator
1 = LA28
2 = LA30
3 = LA30 IPX6
4 = LA31
6 = LA34
7 = LA34 Compact

FUNCTION

- 0 = 1 actuator outwards direction, stops when switch is activated/
inwards direction is always possible (1*NC with diode)
1 = 1 actuator inwards direction, stops when switch is activated/
outwards direction is always possible (1*NC with diode)
2 = 1*NO switch external signal unit/simple switch function
3 = 1*NC switch external signal unit/simple switch function
4 = for OpenBus™ SLS NO with Power Request, H30, only plug type "L1"/ Modular plug
5 = for OpenBus™ SLS NO, no Power Request, H31, only plug type "L1"/ Modular plug
6 = for OpenBus™ SLS NO, no Power Request, H30, only plug type "L1"/ Modular plug
7 = for OpenBus™ SLS NO with Power Request, H29, only plug type "L1"/ Modular plug
8 = for OpenBus™ SLS NO, no Power Request, H29, only plug type "L1"/ Modular plug
9 = for OpenBus™ SLS NO with Power Request, H31, only plug type "L1"/ Modular plug
X = Other

IP DEGREE

- 4 = IP X6 welding
6 = IP X6 washable welding


* Also possible to order other lengths (min. Length 100mm)

Double switch must be ordered as a special article.

Note:

- Cable lengths L1 and L2 in mm can be seen in the cable drawing
- It is no longer possible to order the SLS version fitted with screws

Dimensions




Drawing number: 09144001




Information

- The ultrasonic welded SLS is fully compatible with the SLS fitted with screws.
- All outer dimensions as well as the activation point are unchanged.

Cable lengths



Drawing number: 09144002



Drawing number: 09144003

Contacts

FACTORIES

Denmark - Headquarters
LINAK A/S
Phone: +45 73 15 15 15
Fax: +45 74 45 80 48
Fax (Sales): +45 73 15 16 13
Web: www.linak.com

China
LINAK (Shenzhen) Actuator Systems, Ltd.
Phone: +86 755 8610 6656
Phone: +86 755 8610 6990
Web: www.linak.cn

Slovakia
LINAK Slovakia s.r.o.
Phone: +421 51 7563 444
Web: www.linak.sk

Thailand
LINAK APAC Ltd.
Phone: +66 33 265 400
Web: www.linak.com

USA
LINAK U.S. Inc.
Americas Headquarters
Phone: +1 502 253 5595
Fax: +1 502 253 5596
Web: www.linak-us.com
www.linak-latinamerica.com

SUBSIDIARIES

Australia
LINAK Australia Pty. Ltd
Phone: +61 3 8796 9777
Fax: +61 3 8796 9778
E-mail: sales@linak.com.au
Web: www.linak.com.au

Austria
LINAK Zweigniederlassung - Österreich (Wien)
Phone: +43 (1) 890 7446
Fax: +43 (1) 890 744615
E-mail: info@linak.de
Web: www.linak.at - www.linak.hu

Belgium
LINAK Actuator-Systems NV/SA
(Belgium & Luxembourg)
Phone: +32 (0)9 230 01 09
E-mail: beinfo@linak.be
Web: www.linak.be - www.fr.linak.be

Brazil
LINAK Do Brasil Comércio De Atuadores Ltda.
Phone: +55 (11) 2832 7070
Fax: +55 (11) 2832 7060
E-mail: info@linak.com.br
Web: www.linak.com.br

Canada
LINAK Canada Inc.
Phone: +1 502 253 5595
Fax: +1 416 255 7720
E-mail: info@linak.ca
Web: www.linak-us.com

Czech Republic
LINAK C&S s.r.o.
Phone: +42 058 174 1814
Fax: +42 058 170 2452
E-mail: info@linak.cz
Web: www.linak.cz - www.linak.sk

Denmark - International
LINAK International
Phone: +45 73 15 15 15
E-mail: info@linak.com
Web: www.linak.com

Denmark - Sales
LINAK Danmark A/S
Phone: +45 86 80 36 11
Fax: +45 86 82 90 51
E-mail: linak@linak-silkeborg.dk
Web: www.linak.dk

Finland
LINAK OY
Phone: +358 10 841 8700
E-mail: linak@linak.fi
Web: www.linak.fi

France
LINAK France E.U.R.L
Phone: +33 (0) 2 41 36 34 34
Fax: +33 (0) 2 41 36 35 00
E-mail: linak@linak.fr
Web: www.linak.fr

Germany
LINAK GmbH
Phone: +49 6043 9655 0
Fax: +49 6043 9655 60
E-mail: info@linak.de
Web: www.linak.de

India
LINAK A/S India Liaison Office
Phone: +91 120 4531797
Fax: +91 120 4786428
E-mail: info@linak.in
Web: www.linak.in

Ireland
LINAK UK Limited (Ireland)
Phone: +44 (0)121 544 2211
Fax: +44 (0)121 544 2552
+44 (0)796 855 1606 (UK Mobile)
+35 387 634 6554 (Rep.of Ireland Mobile)
E-mail: sales@linak.co.uk
Web: www.linak.co.uk

Italy
LINAK ITALIA S.r.l.
Phone: +39 02 48 46 33 66
Fax: +39 02 48 46 82 52
E-mail: info@linak.it
Web: www.linak.it

Japan
LINAK K.K.
Phone: 81-45-533-0802
Fax: 81-45-533-0803
E-mail: linak@linak.jp
Web: www.linak.jp

Malaysia
LINAK Actuators Sdn. Bhd.
Phone: +60 4 210 6500
Fax: +60 4 226 8901
E-mail: info@linak-asia.com
Web: www.linak.my

Netherlands
LINAK Actuator-Systems B.V.
Phone: +31 76 5 42 44 40 /
+31 76 200 11 10
E-mail: info@linak.nl
Web: www.linak.nl

New Zealand
LINAK New Zealand Ltd
Phone: +64 9580 2071
Fax: +64 9580 2072
E-mail: nzsales@linak.com.au
Web: www.linak.com.au

Norway
LINAK Norge AS
Phone: +47 32 82 90 90
E-mail: info@linak.no
Web: www.linak.no

Poland
LINAK Polska
LINAK Danmark A/S (Spółka Akcyjna)
Phone: +48 22 295 09 70 /
+48 22 295 09 71
E-mail: info@linak.pl
Web: www.linak.pl

Republic of Korea
LINAK Korea Ltd.
Phone: +82 2 6231 1515
Fax: +82 2 6231 1516
E-mail: info@linak.kr
Web: www.linak.kr

Slovakia
LINAK Slovakia S.R.O.
Phone: +421 51 7563 444
Web: www.linak.sk

Spain
LINAK Actuadores, S.L.u
Phone: +34 93 588 27 77
Fax: +34 93 588 27 85
E-mail: esma@linak.es
Web: www.linak.es

Sweden
LINAK Scandinavia AB
Phone: +46 8 732 20 00
Fax: +46 8 732 20 50
E-mail: info@linak.se
Web: www.linak.se

Switzerland
LINAK AG
Phone: +41 43 388 31 88
Fax: +41 43 388 31 87
E-mail: info@linak.ch
Web: www.linak.ch - www.fr.linak.ch
www.it.linak.ch

Taiwan
LINAK (Shenzhen) Actuator systems Ltd.
Taiwan Representative office
Phone: +886 2 272 90068
Fax: +886 2 272 90096
E-mail: sales@linak.com.tw
Web: www.linak.com.tw

Turkey
LINAK İth. İhr. San. ve Tic. A.Ş.
Phone: +90 312 4726338
Fax: +90 312 4726635
E-mail: info@linak.com.tr
Web: www.linak.com.tr

United Kingdom
LINAK UK Limited
Phone: +44 (0)121 544 2211
Fax: +44 (0)121 544 2552
E-mail: sales@linak.co.uk
Web: www.linak.co.uk

Argentina
Novotec Argentina SRL
Phone: 011-4303-8989 / 8900
Fax: 011-4032-0184
E-mail: info@novotecargentina.com
Web: www.novotecargentina.com

Colombia
MEM Ltda
Phone: +[57] (1) 334-7666
Fax: +[57] (1) 282-1684
E-mail: serviciocliente@memltda.com.co
Web: www.mem.net.co

India
Mechatronics Control Equipments India Pvt Ltd
Phone: +91-44-28558484, 85
E-mail: bala@mechatronicscontrol.com
Web: www.mechatronicscontrol.com

Indonesia
PT. Himalaya Everest Jaya
Phone: +6 221 544 8956 /+6 221 544 8965
Fax: +6 221 619 1925
Fax (Sales): +6 221 619 4658
E-mail: hejplastic-div@centrin.net.id
Web: www.hej.co.id

Israel
NetivTech LTD
Phone: +972 55-2266-535
Fax: +972 2-9900-560
Email: info@NetivTech.com
Web: www.netivtech.com

Singapore
Servo Dynamics Pte Ltd
Phone: +65 6844 0288
Fax: +65 6844 0070
E-mail: servodynamics@servo.com.sg

South Africa
Industrial Specialised Applications CC
Phone: +27 011 466 0346
E-mail: gartht@isagroup.co.za
Web: www.isaza.co.za

United Arab Emirates
Mechatronics
Phone: +971 4 267 4311
Fax: +971 4 267 4312
E-mail: mechtron@emirates.net.ae

DISTRIBUTORS

Terms of use

LINAK® takes great care in providing accurate and up-to-date information on its products. However, the user is responsible for determining the suitability of LINAK products for a specific application. Due to continual development, LINAK products are subject to frequent modifications and changes. LINAK reserves the rights to conduct modifications, updates, and changes without any prior notice. For the same reason, LINAK cannot guarantee the correctness and actual status of imprinted information on its products.

LINAK uses its best efforts to fulfil orders. However, for the reasons mentioned above, LINAK cannot guarantee availability of any particular product at any given time. LINAK reserves the right to discontinue the sale of any product displayed on its website or listed in its catalogues or in other written material created and produced by LINAK, LINAK subsidiaries, or LINAK affiliates. All sales are subject to the 'Standard Terms of Sale and Delivery for LINAK A/S' available on LINAK websites. LINAK and the LINAK logotype are registered trademarks of LINAK A/S. All rights reserved.